



SIMATIC ET 200SP, BaseUnit BU15-P16+A10+2B, BU type A0, Push-in terminals, with 10 AUX terminals, bridged to the left, WxH: 15 mmx141 mm

General information	
Product type designation	BU type A0
HW functional status	From FS06
Supply voltage	
Rated value (DC)	24 V
external protection for power supply lines	Yes; 24 V DC/10 A miniature circuit breaker with type B or C tripping characteristic
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For AUX bus, max.	10 A
For process terminals, max.	2 A
Hardware configuration	
Formation of potential groups	
• New potential group	No
• Potential group continued from the left	Yes
Slots	
• Number of slots	1; Type A0
Isolation	
Isolation tested with	707 V DC (type test)
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Accessories	
Color coding labels	
• for process terminals	CC00 to CC09
• for AUX terminals	CC71 to CC73
• for add-on terminals	does not exist
connection method	
Terminals	
• Terminal type	Push-in terminal
• system-integrated shield connection	Yes; Optional
• Conductor cross-section, min.	0.14 mm²; AWG 26
• Conductor cross-section, max.	2.5 mm²; AWG 14
• Number of process terminals to I/O module	16
• Number of terminals to AUX bus	10

- Number of add-on terminals
- Number of terminals with connection to P1 and P2 bus

0
2

Dimensions

Width	15 mm
Height	141 mm
Depth	35 mm

Weights

Weight, approx.	50 g
-----------------	------

Classifications

	Version	Classification
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



[KC](#)



For use in hazardous locations



[FM](#)

[CCC-Ex](#)



[Miscellaneous](#)

Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application



[CCS \(China Classification Society\)](#)



Environment

last modified:

4/4/2025