



SIMATIC ET 200SP, BaseUnit BU20-P12+A0+4B, BU type B1, Packing unit: 1 unit, push-in terminals, without auxiliary terminals, bridged to the left, WxH: 20 mm x 117 mm

General information	
Product type designation	BU type B1
HW functional status	FS10 and higher
Supply voltage	
Rated value (DC)	See manual
• For P1 and P2 bus	24 V
• For AUX bus	24 V; Equal potential group to P1/P2 bus or PE
• for process terminals	24 V
Rated value (AC)	See manual
• For P1 and P2 bus	230 V
• For AUX bus	230 V; Equal potential group to P1/P2 bus or PE
• for process terminals	230 V
external protection for power supply lines	Yes
Mains filter	
• integrated	No
Current carrying capacity	
up to 60 °C, max.	10 A
For P1 and P2 bus, max.	10 A
For AUX bus, max.	10 A
For process terminals, max.	5 A
Hardware configuration	
Automatic encoding	Yes
Slots	
• Number of slots	1
Potential separation	
between backplane bus and supply voltage	Yes
between process terminals and supply voltage	Yes; Not applicable for process terminals 9 to 12
between power bus and supply voltage	Yes
Isolation	
Isolation tested with	3 100 V DC
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m
connection method	
Terminals	

- Terminal type
- system-integrated shield connection
- Conductor cross-section, min.
- Conductor cross-section, max.
- Number of process terminals to I/O module
- Number of terminals to AUX bus
- Number of add-on terminals
- Number of terminals with connection to P1 and P2 bus

Push-in terminal

No

0.14 mm²; AWG 26

2.5 mm²; AWG 14

12; Pro slot

0

0

0; Pro slot

Dimensions

Width	20 mm
Height	117 mm
Depth	35 mm

Weights

Weight, approx.	48 g
-----------------	------

Classifications

	Version	Classification
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

Approvals / Certificates

General Product Approval	Test Certificates
--------------------------	-------------------



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

other	Environment
-------	-------------

[Confirmation](#)



[Environmental Confirmations](#)

last modified: 4/7/2025