



Single-flash light element, w. built-in electronic flash, blue, 115 V AC, Diameter 70 mm

product brand name	SIRIUS		
product designation	Flashlight element		
design of the product	including light sources		
General technical data			
type of voltage of the operating voltage	AC		
operating voltage			
• 1 at AC at 50 Hz rated value			
• 1 at AC at 60 Hz rated value	115 V		
relative positive tolerance of the operating voltage	10 %		
relative negative tolerance of the operating voltage	-10 %		
reference code according to EN 61346-2	P		
Lamp			
product component light source	Yes		
type of light source	Xenon gas discharge lamp		
design of the optical signal	flash light		
light intensity	20 324 cd		
flash frequency	1 Hz		
number of flashes of light element	4 000 000		
Enclosure			
height	65.5 mm		
width	70 mm		
outer diameter of the signal column element	70 mm		
material	PC		
color	blue		
fastening method	Bayonet		
protection class IP	IP65		
Ambient conditions			
ambient temperature during operation	-20 ... +50 °C		
Approvals Certificates			
General Product Approval		other	Environment



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD4440-0CF>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD4440-0CF>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/8WD4440-0CF>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD4440-0CF&lang=en



-P



last modified:

4/1/2025 