



Figure similar

Integrated signal lamp, single flash light, w. built-in electronic flash, green, 230 V AC, Diameter 70 mm

General technical data		
product designation	Flashlight element	
consumed current maximum	35 mA	
type of voltage of the operating voltage	AC	
operating voltage		
• 1 at AC at 50 Hz rated value	230 V	
• 1 at AC at 60 Hz rated value	230 V	
relative positive tolerance of the operating voltage	10 %	
relative negative tolerance of the operating voltage	-10 %	
reference code according to IEC 81346-2	P	
fastening method	Bayonet / flush mounting	
material	PC; PC/ABS; PA	
color	green	
Mechanical data		
product component light source	Yes	
type of electrical connection	screw terminal	
outer diameter of the signal column element	75 mm	
Lamp		
design of the optical signal	flash light	
type of light source	Xenon gas discharge lamp	
light intensity	20 542 cd	
flash frequency	1 Hz	
number of flashes of light element	4 000 000	
Ambient conditions		
ambient temperature during operation	-20 ... +50 °C	
protection class IP	IP65	
depth	31 mm	
height	66 mm	
width	75 mm	
Certificates/ approvals		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Confirmations](#)

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD5350-0CC>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD5350-0CC>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD5350-0CC>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD5350-0CC&lang=en





last modified:

4/1/2025 