

Labeling plate for snapping on or gluing, on label holder, label size 12.5x27 mm, silver label, black font with inscription: Man O Auto



product brand name		SIRIUS ACT	
product designation		Labeling plate	
product type designation		3SU1	
General technical data			
protection class IP		IP66, IP67, IP69(IP69K)	
shock resistance for railway applications according to EN 61373		Category 1, Class B	
vibration resistance for railway applications according to EN 61373		Category 1, Class B	
Substance Prohibittance (Date)		10/01/2014	
Weight		1 g	
Ambient conditions			
ambient temperature			
• during operation		70 ... -25 °C	
• during storage and transport		80 ... -40 °C	
Environmental footprint			
Environmental Product Declaration(EPD)		Yes	
global warming potential [CO2 eq] total		0.787 kg	
global warming potential [CO2 eq] during manufacturing		0.566 kg	
global warming potential [CO2 eq] during operation		0.235 kg	
global warming potential [CO2 eq] after end of life		-0.015 kg	
Installation/ mounting/ dimensions			
height		12.5 mm	
width		27 mm	
Accessories			
material of accessory		Plastic	
fastening method of label		snap on / stick	
marking of the name plate for command devices		Man O Auto	
shape of the name plate for command devices		rectangular	
color of the label		silver(plate); black (text)	
Approvals Certificates			
General Product Approval		Test Certificates	Maritime application
 EG-Konf.   cULUS  Type Test Certificates/Test Report  URS			
Maritime application		other	Environment



[Confirmation](#)



Environment

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1900-0AC81-0DY0>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1900-0AC81-0DY0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1900-0AC81-0DY0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1900-0AC81-0DY0&lang=en



last modified:

4/2/2025