



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switch. 4-Pole 4-Fuse Fused in a type 1 enclosure (indoor). Rated 600VAC (60A).

General technical data	
mechanical service life (operating cycles) typical	10000
fastening method	SURFACE
product function note	
number of poles	4
suitability for operation	DISCONNECTING MEAN FOR TWO-SPEED / TWO-WINDING MOTORS
Electricity	
ampacity	60 A
supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
ambient temperature during operation maximum	85 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	SIEMENS
product sub brand name	VBII
product type designation	HEAVY DUTY SWITCH
type of electrical connection	MECHANICAL LUGS
Mechanical Design	
design of the housing	TYPE 1
design of the actuating element	SINGLE THROW
material	STEEL
General product approval	
certificate of suitability	UL98

last modified:

9/15/2021 

