

Siemens Low Voltage Circuit Protection Heavy Duty Safety Switch. 1-Pole 2-Wire and positive and negative ground Non-Fused in a type 3R enclosure (outdoor). Rated 1000VDC (200A). Special features: photovoltaic rated, 10000 AIC disconnect.

General technical data	
principle of operation of the actuating element	SINGLE THROW
mechanical service life (operating cycles) typical	8000
fastening method	2 OR 3 POINT MOUNTING HOLES
product function note	
number of poles	1
Electricity	
ampacity	200 A
supply voltage frequency rated value 50/60 Hz	Yes
voltage between phase and Ground (GND) rated value	1000 V
Model	
product brand name	SIEMENS
product type designation	ENCLOSED/SAFETY SWITCH
Mechanical Design	
design of the housing	TYPE 3R
material	Galv. Steel, Painted
General product approval	
certificate of suitability	UL

last modified:

7/18/2024 

