

Siemens low-voltage circuit protection heavy duty safety switches. Type: enclosed, safety switch std: UL V. rating: 600V A. Rating: 800 A F. Rating: 60Hz. 2-3 point mounting holes. O. Cycles: 3500 O. Temperature: (-20F-120F) AMBIENT Temperature environmental conditions: indoors



General technical data	
fastening method	2 OR 3 POINT MOUNTING HOLES
Electricity	
voltage between phase and phase rated value	600 V
Model	
product brand name	SIEMENS
product type designation	ENCLOSED/SAFETY SWITCH
General product approval	
certificate of suitability	UL

last modified: 1/6/2021

