



surge suppressor, RC element, 48-127 V AC, 50/60 Hz, 70-150 V DC, for contactors 3RT2.3, multi-unit packaging, pack = 10 units

product brand name	SIRIUS
product category	Surge suppressor
product designation	RC element
suitability for use	for 3RT2.3 contactors
General technical data	
certificate of suitability	CE / UL / CSA
size of contactor	S2
Substance Prohibitance (Date)	10/01/2014
SVHC substance name	Lead - 7439-92-1
Weight	0.007 kg
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
• at 50 Hz rated value	48 ... 127 V
• at 60 Hz rated value	48 ... 127 V
control supply voltage frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
control supply voltage at DC rated value	70 ... 150 V
design of the surge suppressor	RC element
Ambient conditions	
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C
Installation/ mounting/ dimensions	
mounting position	any
fastening method	clip-on
height	30 mm
width	30 mm
depth	15 mm
Further information	
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875	
Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012	
Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10	
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT2936-1CC00-Z X90	
Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT2936-1CC00-Z X90	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3RT2936-1CC00-Z X90	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)	



