



communications module COM060 accessory for: 3VA61/62

Model	
product brand name	SETRON
product designation	COM060 communication module
accessories	Communication and measurement function
General technical data	
suitability for operation	3VA6 150/250 and COM800
mounting position	Right switch pocket
degree of pollution	3
overvoltage category	I
operating resource protection class	III according to IEC61558
protection class IP	IP20 according to IEC60529
Mechanical Design	
product function	• electronic tripping unit power supply • detection of switch position: On, Off, Tripped • communication with function module • communication with residual current equipment • data exchange with the electronic tripping unit
number of interfaces / of the circuit breaker communication system	1
length / of the supplied connecting cable / for circuit breaker communication system	0.15 m
type of electrical connection / of the circuit breaker communication interface	Spur line via T feeder
total length / of the circuit breaker communication system	20 m
power loss [W] / rated value	2.4 W
consumed current / maximum	0.1 A
height	63 mm
width	29 mm
number of slots	4
depth	33 mm
net weight	90 g
ambient temperature / during operation	• minimum • maximum
ambient temperature / during transport	• minimum • maximum
ambient temperature / during storage	• minimum • maximum

ambient temperature / during storage	
• minimum	-40 °C
• maximum	80 °C

Certificates

General Product Approval	EMV
--------------------------	-----



[Miscellaneous](#)



Test Certificates	Maritime application	other	Environment
-------------------	----------------------	-------	-------------

[Type Test Certificates/Test Report](#)



[Confirmation](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9177-0TB10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9177-0TB10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9177-0TB10


CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





last modified:

7/18/2025 

