

SIEMENS CONTACTOR SUPPRESSOR

Varistor and LED, 24VAC/DC

Art.No.: 2000-68500-4410000

Weight: 0.01

Country of origin: CZ

Model designation: NG00-VL-24-S

24 V AC/DC



48 V AC/DC

VDR + LED

For other configurations and voltages, please inquire.

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text

NG00-VL-24-S

Commercial data

URL Webshop	https://shop.murrelektronik.com/2000-68500-4410000
GTIN	4048879010610
ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-7.1	27371013
ECLASS-8.0	27371013
ECLASS-8.1	27371013
ECLASS-9.0	27371013
ECLASS-9.1	27371013
ECLASS-10.0.1	27371013
ECLASS-10.1	27371013
ECLASS-11.0	27371013
ECLASS-11.1	27371013
ECLASS-12.0	27371013
ECLASS-13.0	27371013
ECLASS-14.0	27371013
ETIM-5.0	EC002498
ETIM-6.0	EC002498
ETIM-7.0	EC002498
ETIM-8.0	EC002498
customs tariff number	85363010
EAN	4048879010610
Packaging unit	1

Electrical data

Damping factor	1.5x UN
----------------	---------

Electrical data | Input

Input voltage AC min.	12 V
Input voltage AC max.	48 V
Input voltage DC min.	12 V
Input voltage DC max.	48 V

Installation | Connection

Connection information	Plug contact
------------------------	--------------

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data | Material data

Material housing	Plastic
Combustibility class housing (UL94)	V-0

Mechanical data | Mounting data

Height	46.4 mm
Width	28 mm
Depth	8.6 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	70 °C