

EOL - Modlink MSDD-set: Frame 4000-68112-0000000,

insert 4000-68000-1500000

Art.No.: 4000-68112-1500000


Weight: 0.322

Country of origin: DE

Model designation: MSDD_1SW_2XPS2+25BU/ST_

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806

ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
customs tariff number	85366990
EAN	4048879036436
EAN	4048879036436
Packaging unit	1
Packaging unit	1

Frame

Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	60 °C
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Material housing	Fine zinc die casting
Coating housing	KTL

SUB-D25

Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	3 A
Current operating max. (UL)	175 mA
Family construction form	SUB-D25
Family type Back side	SUB-D25
Gender	female
Gender Rear	male
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
No. of poles	25

PS2

Connection cross section max.	0,5 mm ²
AWG number max.	20
Operating voltage AC	30 V
Operating voltage DC	30 V
Operating current	1 A
Family construction form	PS2
Family type Back side	PS2
Gender	female
Gender Rear	Solder connection
Looking techniques	Screw locking
No. of poles	6