

COMLIGHT56 LED AMBER STATUS LIGHT

Input 24VDC

Art.No.: 4000-76056-1112000

Weight: 0.06

Country of origin: ID

Model designation: Comlight56-LED-Y

Compact status light
yellow

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-8.0	27110390
ECLASS-9.0	27110350
ECLASS-10.1	27110350
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ETIM-5.0	EC000232
customs tariff number	85319000
customs tariff number	85319000
GTIN	4048879853859
GTIN	4048879853859
Packaging unit	1
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	26 mA

Industrial communication | HMI

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-02

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Luminous intensity	1340 mcd
--------------------	----------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	61 mm
Width	56 mm
Depth	56 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 1	24 V DC (0 V)
PIN 2	0 V (24 V DC)