

MODLINK MSDD SOCKET INSERT AUSTRALIA

240VAC/15A

Art.No.: 4000-68000-0090000

Weight: 0.045

Country of origin: CN

Model designation: Fr.Modul-I-240-15-SC

Australia

Screw terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
customs tariff number	85366990
EAN	4048879038218
EAN	4048879038218
Packaging unit	1
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	35 mm

Environmental characteristics | Climatic

Storage temperature min.	-10 °C
Storage temperature max.	60 °C

Australia

Connection cross section max.	4 mm ²
AWG number max.	12
Operating voltage AC	240 V
Operating current	15 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes