

MODLINK MSDD SOCKET INSERT GREAT BRITAIN

250VAC/13A orange

Art.No.: 4000-68000-0190000

Weight: 0.05

Country of origin: HU

Model designation: Fr.Modul-G-OG-250-13-SC

England (BS) orange

with touch protection

Screw terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
customs tariff number	85366990
EAN	4048879038119
EAN	4048879038119
Packaging unit	1
Packaging unit	1

Mechanical data | Mounting data

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-12

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Height	88 mm
Width	51 mm
Depth	25 mm

Environmental characteristics | Climatic

Storage temperature min.	-10 °C
Storage temperature max.	60 °C

England

Operating voltage AC	250 V
Operating current	13 A
No. of poles	2 + PE
Protection contact present	yes