

MODLINK MSDD DATA INSERT

2xSUB-D9 female/male  
Art.No.: 4000-68000-0200000  
Weight: 0.04  
Country of origin: DE  
Model designation: FR.MODUL 2x9pol. Bu/St

SUB-D9; SUB-D9  
2× SUB-D9 (female/male)

Link to Product

Illustration



Product may differ from Image



Header

Material short textFR.MODUL 2x9pol. Bu/St

Commercial data

|               |                                                    |
|---------------|----------------------------------------------------|
| URL Webshop   | https://shop.murrelektronik.com/4000-68000-0200000 |
| GTIN          | 4048879038102                                      |
| ECLASS-6.0    | 27189217                                           |
| ECLASS-6.1    | 27189217                                           |
| ECLASS-7.0    | 27189217                                           |
| ECLASS-7.1    | 27189217                                           |
| ECLASS-8.0    | 27189217                                           |
| ECLASS-8.1    | 27189217                                           |
| ECLASS-9.0    | 27182806                                           |
| ECLASS-9.1    | 27189217                                           |
| ECLASS-10.0.1 | 27182806                                           |
| ECLASS-10.1   | 27182806                                           |
| ECLASS-11.0   | 27182806                                           |
| ECLASS-11.1   | 27182806                                           |
| ECLASS-12.0   | 27182806                                           |
| ECLASS-13.0   | 27182806                                           |
| ECLASS-14.0   | 27182806                                           |

|                       |               |
|-----------------------|---------------|
| ETIM-5.0              | EC002625      |
| ETIM-6.0              | EC002625      |
| ETIM-7.0              | EC002625      |
| ETIM-8.0              | EC002625      |
| customs tariff number | 85366990      |
| EAN                   | 4048879038102 |
| Packaging unit        | 1             |

**Mechanical data | Mounting data**

|        |       |
|--------|-------|
| Height | 88 mm |
| Width  | 51 mm |
| Depth  | 40 mm |

**Environmental characteristics | Climatic**

|                          |        |
|--------------------------|--------|
| Storage temperature min. | -30 °C |
| Storage temperature max. | 60 °C  |

**SUB-D9**

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| Family construction form              | SUB-D9                                         |
| Gender                                | female                                         |
| No. of poles                          | 9                                              |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| Family type Back side                 | SUB-D9                                         |
| Gender Rear                           | male                                           |
| Operating voltage AC                  | 48 V                                           |
| Operating voltage DC                  | 48 V                                           |
| Operating current                     | 3 A                                            |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42.4 V                                         |
| Current operating max. (UL)           | 175 mA                                         |