

**MODLINK MSDD DATA INSERT**

1×RJ45 + 1xSUB-D9 blind

Art.No.: 4000-68000-1210000

Weight: 0.031

Country of origin: DE

Model designation: FR.MODUL RJ45/45 + Blind

RJ45

1× RJ45, 8-pole metal, CAT5e (female/female)

1× SUB-D9 (blind plug)

**Link to Product**

**Illustration**



Product may differ from Image



| Commercial data |                                                                                                                     |
|-----------------|---------------------------------------------------------------------------------------------------------------------|
| URL Webshop     | <a href="https://shop.murrelektronik.com/4000-68000-1210000">https://shop.murrelektronik.com/4000-68000-1210000</a> |
| GTIN            | 4048879037617                                                                                                       |
| ECLASS-6.0      | 27189217                                                                                                            |
| ECLASS-6.1      | 27189217                                                                                                            |
| ECLASS-7.0      | 27189217                                                                                                            |
| ECLASS-7.1      | 27189217                                                                                                            |
| ECLASS-8.0      | 27189217                                                                                                            |
| ECLASS-8.1      | 27189217                                                                                                            |
| ECLASS-9.0      | 27182806                                                                                                            |
| ECLASS-9.1      | 27189217                                                                                                            |
| ECLASS-10.0.1   | 27182806                                                                                                            |
| ECLASS-10.1     | 27182806                                                                                                            |
| ECLASS-11.0     | 27182806                                                                                                            |
| ECLASS-11.1     | 27182806                                                                                                            |
| ECLASS-12.0     | 27182806                                                                                                            |
| ECLASS-13.0     | 27182806                                                                                                            |
| ECLASS-14.0     | 27182806                                                                                                            |
| ETIM-5.0        | EC002625                                                                                                            |
| ETIM-6.0        | EC002625                                                                                                            |

|          |               |
|----------|---------------|
| ETIM-7.0 | EC002625      |
| ETIM-8.0 | EC002625      |
| EAN      | 4048879037617 |

**Mechanical data | Mounting data**

|        |       |
|--------|-------|
| Height | 88 mm |
| Width  | 51 mm |
| Depth  | 40 mm |

**Environmental characteristics | Climatic**

|                          |       |
|--------------------------|-------|
| Storage temperature min. | 5 °C  |
| Storage temperature max. | 40 °C |

**RJ45**

|                                       |                   |
|---------------------------------------|-------------------|
| Family construction form              | RJ45              |
| Looking techniques                    | Snap-in connector |
| Cable category min.                   | Cat5e             |
| Family type Back side                 | RJ45              |
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42.4 V            |
| Current operating max. (UL)           | 175 mA            |