

MODLINK MSDD SOCKET INSERT CHINA

250VAC/10A screw connection
Art.No.: 4000-68000-3250000
Weight: 0.046
Country of origin: CN
Model designation: Fr.Modul-I-250-10-SC

China (CCC)
Screw terminals
with touch protection

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
customs tariff number	85366990
EAN	4048879037266
EAN	4048879037266
Packaging unit	1
Packaging unit	1
Mechanical data Mounting data	

Height	88 mm
Width	51 mm
Depth	25 mm

Environmental characteristics | Climatic

Storage temperature min.	-30 °C
Storage temperature max.	60 °C

China (CCC)

Connection cross-section solid max.	4 mm ²
Connection cross-section stranded/fine-stranded max.	4 mm ²
Operating voltage AC	250 V
Operating current	10 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes