


Modlink MSDD-set: Frame 4000-68112-0000000,

insert 4000-68000-0040000

Art.No.: 4000-68112-0040000
Weight: 0.334
Country of origin: DE
Model designation: MSDD_1SW_NEMA5-15SK_

Link to Product

Illustration



Product may differ from Image

0
0
0
0
0
0
0
0
0

0
0
0

Header	
Material short text	MSDD_1SW_NEMA5-15SK_
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68112-0040000
GTIN	4048879036610
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879036610
Packaging unit	1
Frame	
Material housing	Fine zinc die casting
Coating housing	KTL
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
USA	
Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	yes
Connection cross section max.	2.5 mm ²
AWG number max.	14
Operating voltage AC	125 V
Operating current	15 A