

Modlink MSDD-set: Frame 4000-68113-0000000,

insert 4000-68000-1210000


Art.No.: 4000-68113-1210000
Weight: 0.311
Country of origin: US
Model designation: MSDD_1MV_RJ45+BL_

Link to Product

Illustration



Product may differ from Image



0
0
0
0
0
0
0
0
0

0

0

0

Header	
Material short text	MSDD_1MV_RJ45+BL_
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68113-1210000
GTIN	4048879036092
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879036092
Packaging unit	1
Frame	
Material housing	Fine zinc die casting
Coating housing	surface finished
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
RJ45	
Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA