

## KDP/R

Weight: 0.057

Country of origin: DE

Model designation: KDP/R M63/19

round (M63)

For sale only in packing units

Cable diameter (19)× 3...5 mm

### Illustration



Product may differ from Image

## Header

Material short text KDP/R M63/19

## Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/4000-70703-0630190">https://shop.murrelektronik.com/4000-70703-0630190</a>
GTIN	4048879031585
ECLASS-6.0	27189217
ECLASS-6.1	27400604
ECLASS-7.0	27400604
ECLASS-7.1	27400604
ECLASS-8.0	27400604
ECLASS-8.1	27400604
ECLASS-9.0	27400604
ECLASS-9.1	27400604
ECLASS-10.0.1	27400604
ECLASS-10.1	27400604
ECLASS-11.0	27400604
ECLASS-11.1	27400604
ECLASS-12.0	27400604
ECLASS-13.0	27400604
ECLASS-14.0	27400604
ETIM-5.0	EC000211
ETIM-6.0	EC000211
ETIM-7.0	EC000211

The information in this Product-PDF has been compiled with the utmost care.  
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-10-04

ETIM-8.0	EC000211
customs tariff number	39269097
EAN	4048879031585
Packaging unit	1
<b>Device protection   Electrical</b>	
Degree of protection (EN IEC 60529)	IP65
<b>Mechanical data   Material data</b>	
Material housing	PA
<b>Mechanical data   Mounting data</b>	
Height	34 mm
Width	71 mm
Depth	71 mm
Mounting method	geschnappt, screwed
Sheet thickness min. (screw mounting)	1.5 mm
Sheet thickness max. (screw mounting)	2 mm
Sheet thickness min. (snap-on mounting)	1.5 mm
Sheet thickness max. (snap-on mounting)	2 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-30 °C
Operating temperature max.	70 °C