

EOL - COMLIGHT57 LED GREEN STATUS LIGHT

Product discontinued

Art.No.: 4000-75057-1113000

Weight: 0.057

Country of origin: ID

Model designation: Comlight57-LED-G

Compact status light
green

[Link to Product](#)

Illustration



Product may differ from Image

Commercial data

ECLASS-6.0	27371220
ECLASS-7.0	27371220
ECLASS-8.0	27371220
ECLASS-9.0	27371220
ETIM-5.0	EC000232
customs tariff number	85318070
customs tariff number	85318070
EAN	4048879402170
EAN	4048879402170
Packaging unit	1
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	23 mA

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	61 mm
Width	57 mm
Depth	57 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Family construction form	M12
Gender	male
Coding	A
No. of poles	4
PIN 3	BU 0 V
PIN 4	BK 24 V DC