

MODLIGHT50/70 MAGNET BASE WITH M12 8-POLE

Side cable entry

Art.No.: 4000-75070-0000921
Weight: 0.381
Country of origin: DE
Model designation: Modlight50/70-Magnetfuß M12

Magnet base
with M12 flange plug connector (8-pole)

Link to Product

Illustration



Product may differ from Image

Header	
Material short text	Modlight50/70-Magnetfuß M12
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-75070-0000921
GTIN	4048879031080
ECLASS-6.0	27371235
ECLASS-6.1	27371235
ECLASS-7.0	27371235
ECLASS-7.1	27371235
ECLASS-8.0	27371235
ECLASS-8.1	27371235
ECLASS-9.0	27371235
ECLASS-9.1	27371235
ECLASS-10.0.1	27371235
ECLASS-10.1	27371235
ECLASS-11.0	27371235
ECLASS-11.1	27371235
ECLASS-12.0	27371235
ECLASS-13.0	27371235
ECLASS-14.0	27371235
ETIM-5.0	EC001154
ETIM-6.0	EC001154
ETIM-7.0	EC001154
ETIM-8.0	EC001154
customs tariff number	85319000

EAN	4048879031080
-----	---------------

Packaging unit	1
----------------	---

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
-------------------------------------	------

Mechanical data | Material data

Material housing	Aluminum
------------------	----------

Color housing	black
---------------	-------

Mechanical data | Mounting data

Height	35 mm
--------	-------

Width	70 mm
-------	-------

Depth	70 mm
-------	-------

Connection type 2

Family construction form	M12
--------------------------	-----

No. of poles	5
--------------	---

Coding	A
--------	---

Gender	male
--------	------

PIN 1	n.c.
-------	------

PIN 2	n.c.
-------	------

PIN 3	0 V DC
-------	--------

PIN 4	24 V DC
-------	---------

PIN 5	FE
-------	----

Family construction form	M12
--------------------------	-----

No. of poles	8
--------------	---

Coding	A
--------	---

Gender	male
--------	------