

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

ETIM-5.0	EC000232
ETIM-6.0	EC000232
ETIM-7.0	EC000232
ETIM-8.0	EC000232
customs tariff number	85319000
EAN	4048879853859
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	26 mA

HMI | Illumination properties

Luminous intensity	1,340 mcd
--------------------	-----------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	61 mm
Width	56 mm
Depth	56 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Family construction form	terminal
No. of poles	2
Gender	female
Connection	Spring clamp terminals FK
PIN 1	24 V DC (0 V)
PIN 2	0 V (24 V DC)