

EUROCARD HOLDER

SKP 64/IC

Art.No.: 63043

Weight: 0.358

Country of origin: CZ

Model designation: SKP 64/IC(a,e)

Screw terminals

64-pole C (EN 60603)

Row a, c

250 V AC


With the vertical snap adapter SASA 135 Art.-No. 63900 the holder can be mounted at right-angles on the rail.

The D2 size is for a card without a front plate.

To insert the card first press down the 2 yellow buttons. Then slide the Eurocard into the guide slots pushing until fully engaged. The card is now locked into position. It can be removed by pressing down on the 2 yellow buttons.

[Link to Product](#)

Illustration



Product may differ from Image



Header

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-10-05

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Material short text	SKP 64/IC(a,e)
Commercial data	
URL Webshop	https://shop.murrelektronik.com/63043
GTIN	4048879042086
ECLASS-6.0	27260710
ECLASS-6.1	27260704
ECLASS-7.0	27440402
ECLASS-7.1	27440402
ECLASS-8.0	27440402
ECLASS-8.1	27440402
ECLASS-9.0	27460201
ECLASS-9.1	27440402
ECLASS-10.0.1	27440402
ECLASS-10.1	27440402
ECLASS-11.0	27460201
ECLASS-11.1	27460201
ECLASS-12.0	27460201
ECLASS-13.0	27460201
ECLASS-14.0	27460201
ETIM-5.0	EC002780
ETIM-6.0	EC002780
ETIM-7.0	EC002780
ETIM-8.0	EC002780
customs tariff number	85366990
EAN	4048879042086
Packaging unit	1
Electrical data Supply	
Operating voltage AC	250 V
Operating current max.	2 A
Installation	
Connection cross-section solid max.	4 mm ²
Installation Pin assignment	
No. of poles	64
Device protection Electrical	
Overvoltage category (EN 60664-1)	I
Device protection Media	
Flame resistance	flame retardant
Mechanical data	
Type of socket connector	C (EN 60603)
Mechanical data Material data	
Material housing	Plastic
Mechanical data Mounting data	
Height	137 mm
Width	63 mm
Depth	170 mm
Mounting method	geschnappt, screwed
Suitable for mounting type	(EN 60715), mounting rail