

MST 1-PHASE SAFETY TRANSFORMER

P: 400VA IN: 230/400VAC OUT: 24VAC

Art.No.: 6686327

Weight: 5.15

Country of origin: CZ

Model designation: MST 0400-230-400/24 SPRING CLAMP



Single-phase safety transformer

400 VA

Spring clamp terminals

Isolation class T 40/B

Other voltages on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

MST 0400-230-400/24 SPRING CLAMP

Commercial data

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-10-04

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

URL Webshop	https://shop.murrelektronik.com/6686327
GTIN	4048879066174
ECLASS-6.0	27031302
ECLASS-6.1	27031302
ECLASS-7.0	27031302
ECLASS-7.1	27031302
ECLASS-8.0	27031302
ECLASS-8.1	27031302
ECLASS-9.0	27031302
ECLASS-9.1	27031302
ECLASS-10.0.1	27031302
ECLASS-10.1	27031302
ECLASS-11.0	27031302
ECLASS-11.1	27031302
ECLASS-12.0	27031302
ECLASS-13.0	27031302
ECLASS-14.0	27031302
ETIM-5.0	EC002486
ETIM-6.0	EC002486
ETIM-7.0	EC002486
ETIM-8.0	EC002486
customs tariff number	85043180
EAN	4048879066174
Packaging unit	1
Electrical data	
Security level	SELV
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	
Input voltage 1 AC	230 V
Input voltage 2 AC	400 V
Input current at input voltage 1 AC	1.95 A
Input current at input voltage 2 AC	1.1 A
Inrush current at input voltage 1	52.3 A
Inrush current at input voltage 2	30.2 A
Short-circuit current at input voltage 1	43 A
Short-circuit current at input voltage 2	24.9 A
Electrical data Output	
Output voltage adjustable	no
Output voltage AC	24 V
Power rating AC max.	400 VA
Device protection Electrical	
Insulation test voltage input - output	4 kV
Mechanical data Mounting data	
Height	104.2 mm
Width	120 mm
Depth	123 mm
Suitable for mounting type	Schlüssellochabhängung
Mounting dimension a	86.5 mm
Mounting dimension b	90 mm
Mounting dimension c	58 mm

Diameter bore	5.8 mm
---------------	--------

Length bore	10 mm
-------------	-------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	40 °C
----------------------------	-------

Storage temperature min.	-40 °C
--------------------------	--------

Storage temperature max.	80 °C
--------------------------	-------

Conformity

Product standard	EN 61558-2-4, EN 61558-2-6, EN 62041 category 0
------------------	---

Connection type 3

Connection type 1	Input
-------------------	-------

Connection type 2	Output
-------------------	--------

Family construction form	terminal
--------------------------	----------

No. of poles	3
--------------	---

Gender	female
--------	--------

Connection	Screw terminals SK
------------	--------------------

PIN 2	230 V
-------	-------

PIN 3	400 V
-------	-------

Family construction form	terminal
--------------------------	----------

No. of poles	2
--------------	---

Gender	female
--------	--------

Connection	Screw terminals SK
------------	--------------------

PIN 2	24 V DC
-------	---------

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	metallic
-----------------------	----------

Connection	Screw terminals SK
------------	--------------------

PIN 1	PE
-------	----