

EOL - MKDP 24/12 Cable entry plate

Product discontinued

Art.No.: 7000-90201-2412000

Weight: 0.101

Country of origin: DE

Model designation: MKDP 24/12

Size 24

Cable diameter (12)× 8...12 mm

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27400569
ECLASS-11.1	27400569
ECLASS-12.0	27400569
ETIM-5.0	EC001855
customs tariff number	39269097
EAN	4048879568524
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP66
-------------------------------------	------

Mechanical data | Material data

Material housing	PA
Material gasket	TPE

Mechanical data | Mounting data

Height	147,5 mm
Width	59,5 mm
Depth	25 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	100 °C

Conformities, approvals, certificates

Combustibility class (UL94)	V-0
-----------------------------	-----