

Adaptor M12 male on top / MSUD valve plug A-18mm

4-pol. A-cod.

Art.No.: 7000-41361-0000000

Weight: 0.04

Country of origin: CZ

Model designation: MSZLI-A

Form A (18 mm) – M12, connector top entry

24 V AC/DC $\pm 25\%$




for pressure switches



LED (yellow/green)

4-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product**Illustration**



Product may differ from Image

Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-41361-0000000
customs tariff number	85366990
EAN	4048879144650
Packaging unit	1
Electrical data Supply	
Operating voltage AC	24 V
Operating voltage AC min.	18 V
Operating voltage AC max.	30 V
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Current operating per contact max.	4 A
Cut-off peak voltage max.	55 V
Installation Connection	
Tightening torque	0.4 Nm
Mounting set	M3x31
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Rated surge voltage	0.8 kV
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	90 °C
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.