



M12-PANEL FEED THROUGH 5 POLE B-CODED

Art.No.: 7000-44111-0000000
Weight: 0.027
Country of origin: CZ
Model designation: MSBBSV-BA-U


Control cabinet entry system
Male - female
M12, 5-pole
B-coded
shielded

Link to Product

Illustration



Product may differ from Image



Side 1	
Family construction form	M12
Coding	B
Side 2	
Family construction form	M12
Coding	B
Commercial data	
ECLASS-6.0	27279220

ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-8.0	27440103
ECLASS-9.0	27440109
ECLASS-10.1	27440109
ECLASS-11.1	27440109
ECLASS-12.0	27440109
ETIM-5.0	EC001855
customs tariff number	85366990
customs tariff number	85366990
customs tariff number	85366990
EAN	4048879141420
EAN	4048879141420
EAN	4048879141420
Packaging unit	1
Packaging unit	1
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	60 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A

Installation | Connection

Tightening torque	0,6 Nm
Mounting set	M16 x 1.5

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65, IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	2
Rated surge voltage	1,5 kV
Material group (IEC 60664-1)	I

Mechanical data | Material data

Material housing	Brass
Coating housing	nickel plated

Mechanical data | Mounting data

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.