

MKDP 24/00 cable entry system

Product discontinued

Art.No.: 7000-90201-2400000

Weight: 0.101

Country of origin: DE

Model designation: MKDP 24/00

Size 24

Blind plate

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27400590
ECLASS-11.1	27400592
ECLASS-12.0	27400592
ETIM-5.0	EC001004
customs tariff number	39269097
EAN	4048879611718
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP66
-------------------------------------	------

Mechanical data | Material data

Material housing	PA
Combustibility class (UL94)	V-0
Material gasket	TPE

Mechanical data | Mounting data

Height	147,5 mm
Width	59,5 mm
Depth	25 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
----------------------------	--------

Operating temperature max. 100 °C