

## MKDP 24/11 Cable entry plate

Product discontinued

Art.No.: 7000-90201-2411000

Weight: 0.101

Country of origin: DE

Model designation: MKDP 24/11

Size 24

Cable diameter (4)× 3...6.5 mm, (4)× 5...9.2 mm, (3)× 14...20 mm

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27279221      |
| ECLASS-7.0            | 27440104      |
| ECLASS-8.0            | 27440104      |
| ECLASS-9.0            | 27440102      |
| ECLASS-10.1           | 27400569      |
| ECLASS-11.1           | 27400569      |
| ECLASS-12.0           | 27400569      |
| ETIM-5.0              | EC001855      |
| customs tariff number | 39269097      |
| customs tariff number | 39269097      |
| EAN                   | 4048879568517 |
| EAN                   | 4048879568517 |
| Packaging unit        | 1             |
| Packaging unit        | 1             |

#### Device protection | Electrical

|                                     |      |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP66 |
|-------------------------------------|------|

#### Mechanical data | Material data

|                             |     |
|-----------------------------|-----|
| Material housing            | PA  |
| Combustibility class (UL94) | V-0 |
| Material gasket             | TPE |

#### Mechanical data | Mounting data

|        |          |
|--------|----------|
| Height | 147,5 mm |
| Width  | 59,5 mm  |

|       |       |
|-------|-------|
| Depth | 25 mm |
|-------|-------|

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -30 °C |
|----------------------------|--------|

|                            |        |
|----------------------------|--------|
| Operating temperature max. | 100 °C |
|----------------------------|--------|