




RK ROSE+KRIEGER

A Phoenix Mecano Company

RK Monitor Mounting

Industry grade with universal
or VESA interface




RK Monitor Mounting

All purpose mounting for monitors, touch panels and operating units

This mounting for monitors, touch panels and other operating units is flexible, offers many degrees of freedom and thus can be used universally. Due to compatibility to RK Connecting Technology as well to the RK Profile System most different connections are realizable.

Ideal range of applications:

- General industrial applications
- Plants and machines
- Control centers
- Ergonomic work stations



Features

- Choice of user-specific or VESA-standard monitor connection
- High-strength materials guarantee a long-term load-bearing capacity of up to 25 kg, for reliable processes
- Highly ergonomic thanks to personalised height adjustment
- Optimum adjustment of the field of vision thanks to side-turning
- rotary flange and ball joint: vibration-proof locking in 15° increments
- compact: fixing principle with half shells (suitable for retrofitting and extensions) reducing bushes available (round or square 20, 25, 30mm)
- Connects to aluminium profile, and thus also to the machine frame using slot stones
- Universal mounting holes facilitate simple wall mounting

Table of contents



RK ROSE+KRIEGER




Versions	Rotary flange monitor mounting p. 4
	Ball joint monitor mounting p. 4
	Monitor mounting compact p. 5
	Console monitor mounting p. 6
	Dual-ball monitor mounting p. 7
	Dual-ball pivoting monitor mounting p. 7
Fixing	Wall console p. 8
	Profile console p. 8
	Support arm single p. 9
	Support arm double p. 10
	Support arm double height adjustable. p. 11
	Support arm telescope p. 12
	Support arm telescope height adjustable. p. 14
Modules	Monitor floor stand adjustable p. 16
	Monitor floor stand stationary p. 20
Accessories	Adaptor plate VESA 50/75 p. 28
	Adaptor plate VESA 75/100 p. 28
	Keyboard tray p. 29
	Tablet holder p. 30
	Smartphone holder p. 31
	Lockable steering roller p. 32
	Vario-Quick holding block p. 32
	Reducing bushes p. 33
	Reducing inserts p. 33
	Clamping lever p. 34
	Cable straps with velcro p. 34
Applications	Monitor Mounting p. 24

Versions

Rotary flange monitor mounting



Locking in 15° - steps






Code No.	Weight	max. load
193000030C11	370 g	25 kg

*Other cross-sections by reducing bushes (see page 33)

Ball joint monitor mounting



Locking in 15° - steps




Code No.	Weight	max. load
193000042C11	342 g	10 kg

*Other cross-sections by reducing bushes (see page 33)



RK ROSE+KRIEGER

Monitor mounting compact



Code No.	Weight	max. load
193000052C11	290 g	10 kg

*Other cross-sections by reducing inserts (see page 33)






Versions



NEW Console monitor mounting



Locking in 15° - steps






Code No.	Weight	max. load	
		dynamic	static
193000378C19	284 g	3 kg	10 kg






RK ROSE+KRIEGER

NEW Dual-ball monitor mounting



Code No.	Weight	max. load	
		dynamic	static
193000368C19	310 g	3 kg	10 kg




NEW Dual-ball pivoting monitor mounting



Code No.	Weight	max. load	
		dynamic	static
193000388C19	391 g	3 kg	10 kg




Fixing

Wall console



Code No.	Weight
193000358C66	306 g


Profile console



Includes:
Complete with fixing set for
slot geometry 40

Code No.	Weight
193000298C66	270 g

Includes:
Complete with fixing set for
slot geometry 40





Code No.	Weight	max. load
193000018C66	610 g	10 kg

Fixing

Support arm double

Includes:
Complete with fixing set for
slot geometry 40



Code No.	Weight	max. load
193000028C66	1030 g	25 kg



RK ROSE+KRIEGER

**Support arm double
height adjustable**

Includes:



Complete with fixing set for
slot geometry 40

Features:

Travel 400mm max. (30 mm steps)

Toolless manual adjustment

Safe locking by a spring-loaded
stop bolt






Code No.	Weight	max. load
193000068C66	2040 g	10 kg



Fixing

Support arm telescope

Includes:
Complete with fixing set for
slot geometry 40



Code No.	Weight	max. load
193000048C66	1610 g	5 kg




Fixing

Support arm telescope
height adjustable




Includes:
Complete with fixing set for lot geometry 40

- Features:**
- Travel 400mm max. (30 mm steps)
 - Toolless manual adjustment
 - Safe locking by a spring-loaded stop bolt



Code No.	Weight	max. load
193000058C66	2640 g	5 kg



Modules


Monitor floor stand adjustable

Delivery includes: pre-assembled kit

Features:

- Travel 400mm max. (31mm steps)
- Manual adjustment without tools of the work surface with tie rod support
- Safe locking of the height adjustment by spring-loaded locking bolt
- Stable construction with adjustable feet, optionally with swivel castors (page <?>)
- Coated working surface (0,30m²)
- Integrated cable channel
- Mounting for monitor pre-assembled, optionally combinable with all RK monitor mountings






Code No.	Weight
193000078C66	22,2 kg

Modules

Monitor floor stand adjustable





Height adjustment for monitors



Cable guide



Height adjustment
table top (locking bolt)



Optional: Lockable swivel castor (page 22)



Tie rod

Modules

NEW Monitor floor stand stationary

Features:

- Central column made of high-grade BLOCAN® aluminium profile
- Profile slots (10 mm) make it easy to fasten a range of different modules
- Individual equipping with RK modules e.g. coated table top (0.30 m²), various mounts for monitors, keyboard shelf (height-adjustable), integrated cable channel
- Sturdy aluminium base for stability and durability




Scope of delivery:

BLOCAN® aluminium profile 80x80 mm
Base bracket BAK 80,
set screws M8x25 for fastening
(slot profile in base bracket)



NEW Monitor floor stand stationary
with base bracket



High performance anchor
Drilling diameter 12 mm,
length 110 mm



Code No.	Type	Weight
193000398C66__	monitor floor stand stationary	8,791

Code No.	Type	lot sizes
4016611	HLA	4, 8, 12... pcs.

RK Monitor Mounting

Modules

NEW Monitor floor stand stationary






Monitor Mounting


- Secure mounting for monitor or display device
- Swivelling, rotatable and height-adjustable

Support arm/swivel arm

- Ideal for flexible positioning
- Double, telescoping, height-adjustable (see page 14)



Keyboard tray (see page 29)



Cable channel

- Simple and safe routing of supply lines (see page)




Table Top


- Work surface for writing or depositing objects (see page 24)

See also accessories from page 24.

Accessories Monitor floor stand stationary



Table top

Scope of delivery: Including fixing kit



Code No.	Type	Weight	max. load
193000408C66	table top stationary	4,48 kg	20 kg

Cable channel




Code No.	Profile	Type	Weight
4F55A00	KK-40x20, Cut to size as required	Channel with fixing holes	0,609 kg/m

Cable mounting clip

Material: PA-GF30

Assembling the channel

Easy assembly (no profile drilling) with BLOCAN profiles.



Code No.	for KK-Profile	lot sizes
4E185031	all	10, 20, 30... pcs.

Accessories Monitor floor stand stationary

Order instruction:


- Purchase only in lot sizes and a multiple of that, see product table below

Caps (plastic) for aluminium profile column

- For closing the aluminium profile column



Black RAL 9005*



[mm]

Code No.	Type	A	C	lot sizes
4040421	80x80	80	4	10, 20, 30... pcs.

*More colours, see catalogue „Profile Technology BLOCAN®, page 98


Cover profile for aluminium profile column

- For flush covering the longitudinal grooves in the aluminium profile column

Material: plastic



Black RAL 9005*



Code No.	Type	Colour
4000570	2 m-bar	Schwarz



*More colours, see catalogue „Profile Technology BLOCAN®, page 101

Application





Accessories

Adaptor plate VESA 50/75




Code No.	Weight
94372	67 g

Adaptor plate VESA 75/100



Code No.	Weight
94371	80 g

Keyboard tray




Designed for Support arm double and
Support arm double height adjustable



Code No.	Weight
193000038C66	2500 g

Accessories

Tablet holder



Delivery includes: fixing set for RK monitor mounting



Code No.	adjustment range
193000052C66	from 125 to 190 mm







RK ROSE+KRIEGER

Smartphone holder

Delivery includes:

including fastening 30 mm round tube and fastening to RK Rose+Krieger Profile system (40 mm groove geometry)




Code No.	adjustment range
193000038C69	from 125 (5 inch) to 185 (7,25 inch) mm

Accessories

Lockable swivel castor

Material: galvanized steel
Includes: fixing set for Monitor floor stand adjustable



Code No.	Weight
90503	340 g


Order instruction:

- Purchase only in lot sizes and a multiple of that, see product table below



- For fixing cables and hoses
 - It is possible to insert it into the profile slot retrospectively
- Material: Black plastic

Vario-Quick holding block K/KK

Version K



Version KK



Code No.	Version	lot sizes	Suitable for
40181251	Holding block K	10, 20, 30... piece	40 slot geometry*
40181271	Holding block KK	10, 20, 30... piece	40 slot geometry*



Order instruction:

- Purchase only in lot sizes and a multiple of that, see product table below


Reducing bushes for monitor mounting



Version „R“



Version „V“




[mm]

Code No.	Version	lot sizes	A + 0,1
96204AC	R20	5, 10, 15... piece	20,25
96206AC	R25	5, 10, 15... piece	20,25
96208AC	V20	5, 10, 15... piece	20,25


Reducing inserts for monitor mounting



Version „R“



Version „V“



[mm]


Code No.	Version	lot sizes	A
963000AC	R20	5, 10, 15... piece	20,25
963002AC	R25	5, 10, 15... piece	25,25
963004AC	R30	5, 10, 15... piece	30,25
963001AC	V20	5, 10, 15... piece	20,25
963003AC	V25	5, 10, 15... piece	25,25

Accessories

Clamping lever

- The clamping lever enables the re- adjustment of the clamping elementp. This can be done by easy exchange of the cylinder screw.
- By lifting the grip, the free movement of the serration toothing enables the clamping lever to wing into the desired position. The grip moves into its original position when released.

Material: Grip made of polyamide black, screws -stainless steel




(Symbolic representation)

[mm]									
Code No.	Type	A	B	D	E	H	K	L	M
902381	20-30	65	35	M8	14	25	13	4	19,5

Order instruction:


- Purchase only in pack quantities, see catalogue

Cable straps with velcro



Code No.	Scale of pack quantities
91815	5, 10, 15... piece

Applications



RK Rose+Krieger GmbH
Connecting and positioning systems
Potsdamer Straße 9
32423 Minden, Germany
+49 571 9335-0
info@rk-online.de
www.rk-rose-krieger.com



Learn more