



Product: [5502FL](#)

Fire Alarm, #22-4c BC, Shielded, FPLR

Product Description

Fire Alarm Cable, Riser-FPLR, 4-22 AWG stranded bare copper conductors with polyolefin insulation, overall Beldfoil® shield, PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Fire Alarm, Monitor/Detection, Circuits: Audio, Control, Initiating, Notification, Noisy Environment
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	22 AWG	7x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PO - Polyolefin	0.008 in (0.20 mm)	0.045 in (1.1 mm)	Black, Red, Brown, Blue

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.146 in	Yes

Overall Cable Diameter (Nominal):	0.146 in
-----------------------------------	----------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	16.4 Ohm/1000ft	22.5 pF/ft (73.8 pF/m)	40.5 pF/ft (133 pF/m)	2.2 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
2.19 in (55.6 mm)	2.19 in

Max. Pull Tension:	41.9 lbs (19.0 kg)
Bulk Cable Weight:	16 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL1666 Riser, FT4
NEC / UL Compliance:	Article 760, FPLR
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6502FL

History

Update and Revision:	Revision Number: 0.176 Revision Date: 05-05-2023
----------------------	--

Part Numbers

Variants

Item #	Color	UPC
5502FL 002U1000	Red	612825163312

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.