



Product: [5626UG](#)

Nurse Call & Paging, #24-8c, BC, Unshielded, CM

Product Description

Nurse Call & Paging Cable, Rated-CM, 8-24 AWG solid bare copper conductors with polyolefin insulation, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Nurse Call, Commercial Sound, Annunciators, Voice Systems, Paging
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	8	24 AWG	Solid	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.0065 in (0.17 mm)	0.033 in mm	Yellow, Blue, Black, Orange, Red, Green, White, Purple

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.030 in (0.76 mm)	.093 x .324 in

Overall Cable Diameter (Nominal):	0.093 x 0.324 in
-----------------------------------	------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
32.4 Ohm/1000ft	17 pF/ft (56 pF/m)	1.4 Amps per Conductor at 25°C (10°C Temperature Rise)

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-25°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
0.30 in (7.6 mm)	0.30 in

Max. Pull Tension:	44 lbs (20 kg)
--------------------	----------------

Bulk Cable Weight:	25 lbs/1000ft
--------------------	---------------

Standards and Compliance

Environmental Suitability:	Indoor Rated (Not Riser or Plenum), Indoor, Outdoor - Black only, Aerial - Black only, When supported by messenger wire
Flammability / Reaction to Fire:	UL 1685 UL Loading, UL 1685 Vertical Tray
NEC / UL Compliance:	Article 800, CM
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6626UG

History

Update and Revision:	Revision Number: 0.345 Revision Date: 05-31-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
5626UG F6H1000	Gray, Dark Pearl	Reel	1,000 ft	612825164807	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.