



Product: [7961A](#)

DataTuff® Cat 5e, 1 Quad (2 Pr) #22 Str TC, PO Ins, OS+TC Brd, PVC Jkt, CMG CMX-Outdoor

[Request Sample](#)

Product Description

Industrial Ethernet Cat 5e, 1 Quad (2 Pair) 22AWG (7x30) Tinned copper, PO Insulation , Overall Belfoil®+Tinned Copper Braid(85%) Shield, PVC Outer Jacket, CMG CMX-Outdoor

Technical Specifications

Product Overview

Suitable Applications:	PROFINET, outdoor, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
------------------------	---

Construction Details

Conductor				
Element	Size	Stranding	Material	No. of Elements
Quad(s)	22 AWG	7x30	TC - Tinned Copper	1

Insulation	
Material	Color Code
PO - Polyolefin	White, Blue, Yellow, Orange

Inner Jacket	
Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.164 in (4.17 mm)

Outer Shield		
Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	85%

Outer Jacket		
Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.272 in (6.91 mm)	No
Overall Cable Diameter (Nominal):		
0.272 in (6.91 mm)		

Electrical Characteristics

Electricals	
Max. Conductor DCR	Max. Capacitance Unbalance
57 Ohm/km (17 Ohm/1000ft)	150 pF/ft

Delay	
Max. Delay	Nom. Velocity of Prop.
552 ns/100m	70%

High Frequency									
Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]
1	2.1 dB/100m	65.3	62.3	63.2	63.8	60.8	23	100 ± 20.2	105 ±10

4	4.0 dB/100m	56.3	53.3	56.3	51.7	48.7	23	100 ± 14.2	100 ±10
8	5.6 dB/100m	51.8	48.8	46.2	45.7	42.7	23	100 ± 11.3	100 ±10
10	6.3 dB/100m	50.3	47.3	43.9	43.8	40.8	25	100 ± 11.3	100 ±10
16	8.0 dB/100m	47.3	44.3	35.2	39.7	36.7	25	100 ± 11.3	100 ±10
20	9.0 dB/100m	45.8	42.8	36.5	37.7	34.7	25	100 ± 11.3	100 ±10
25	10.1 dB/100m	44.3	41.3	34.2	35.8	32.8	25.5	100 ± 11.3	100 ±10
31.25	11.4 dB/100m	42.9	39.9	31.3	33.9	30.9	23.6	100 ± 13.2	100 ±10
62.5	16.5 dB/100m	38.4	35.4	21.6	27.8	24.8	21.5	100 ± 16.9	100 ±10
100	21.3 dB/100m	35.3	32.3	17.1	23.8	20.8	20.1	100 ± 20.0	100 ±10

Voltage

UL Voltage Rating
300 V (CMG, CMX-Outdoor), 600 V (AWM 21047)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
60°C	-40°C To +80°C	-20°C To +60°C	-40°C To +80°C

Bend Radius

Stationary Min.
2.560 in (65.02 mm)

Max. Pull Tension:	55 lbs (25 kg)
Bulk Cable Weight:	43 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL 1685 (UL Loading), FT4, IEEE 1202 Vertical Tray Flame Test, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG, CMX-Outdoor, ITC, PLTC
AWM Compliance:	AWM 21047
CEC / C(UL) Compliance:	CMX-Outdoor;CMG
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-6
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Operating Temperature subject to length de-rating. Cable passes -40C Cold Bend per UL 1581. Limits below 4 MHz are for information only.
--------	--

History

Update and Revision:	Revision Number: 0.432 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN
7961A.00305	Green	Reel	305 m	8719605016799
7961A.00610	Green	Reel	610 m	8719605016805
7961A 1SW1000	Green, RAL 6018			612825367314
7961A 1SW2000	Green, RAL 6018			612825367321

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.