



Product: [83905](#)

Type K Thermocouple, 1 Pr #20 Sol, FEP Ins Yel, Red, Brn FEP Jkt, CL3P 200C PLTC SUN RES

[Request Sample](#)

Product Description

Type K Thermocouple, 1 Pair 20AWG (Solid) Chromel+Alumel, FEP Insulation Yel, Red Color Code, Brown FEP Outer Jacket, CL3P 200C PLTC SUN RES

Technical Specifications

Product Overview

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...),low voltage digital control (24v, ...), encoders, control circuits, distributed control
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	20	Solid	Chromel & Alumel

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene	0.01 in (0.25 mm)	0.052 in (1.3 mm)	Yellow and Red

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.012 in (0.30 mm)	0.128 in (3.25 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR
Chromel	400 Ohm/1000ft
Alumel	161 Ohm/1000ft (528 Ohm/km)

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
200°C	-70°C To +200°C

Bend Radius

Stationary Min.	Installation Min.
1.28 in (32.5 mm)	1.28 in (32.5 mm)

Max. Pull Tension:	58 lbs (26 kg)
Bulk Cable Weight:	12 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum)
NEC / UL Compliance:	Article 725, CL3P, PLTC
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ISA MC 96.1-1982 Type K

Product Notes

Notes:	Chromel & Alumel = ""Chromel and Alumel are Hoskins Manufacturing Company trademarks.""
--------	---

History

Update and Revision:	Revision Number: 0.576 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
83905 001100	Brown	Reel	100 ft	612825205852	
83905 001500	Brown	Reel	500 ft	612825205876	
83905 0011000	Brown	Reel	1,000 ft	612825205869	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.