



Product: [9239](#) 

Audio Coax, Low Noise, RG-174, 26 AWG Str BCCS, 90% TC Brd, PVC Jkt

Product Description

Audio Coax, Low Noise, RG-174, 26 AWG (7x34) Bare Copper Covered Steel Conductor, PE Insulation, PE Conductive Layer, 90% Tinned Copper Braid Shield, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Low noise microphone, Analog audio, Instrumentation
------------------------	---

Construction Details

RG Type:	174
----------	-----

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	26 AWG	7x34	0.006 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	0.044 in (1.1 mm)	Clear, Black
PVC - Polyvinyl Chloride (Conductive)	0.056 in (1.4 mm)	

Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Braid	Tinned Copper (TC)	90%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.101 in (2.57 mm)

Overall Cable Diameter (Nominal):	0.101 in (2.57 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Velocity of Prop.
89.6 Ohm/1000ft	14 Ohm/1000ft (46 Ohm/km)	44 pF/ft (140 pF/m)	57%

Voltage

Voltage Rating
1100 V

Electrical Characteristics Notes:	NBS Low Noise Test (Modified), MIL-DTL-17J Paragraph 4.8.14, 8 mV Peak to Peak Max
-----------------------------------	--

Mechanical Characteristics

Temperature

Operating
-40°C To +60°C

Bend Radius

Stationary Min.	Installation Min.
1.01 in (25.7 mm)	1.01 in (25.7 mm)

Max. Pull Tension:	43 lbs (20 kg)
Bulk Cable Weight:	7 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Not recommended for RF use. Low noise audio applications.
--------	---

History

Update and Revision:	Revision Number: 0.258 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
9239 010100	Black	Reel	100 ft	612825358824
9239 010500	Black	Reel	500 ft	612825358855
9239 0101000	Black	Reel	1,000 ft	612825357728

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.