

## AX102257 Faceplates and Panels - KeyConnect Faceplates 12-Port w/ID Windows Double-Gang



For more Information  
please call

1-800-Belden1



### General Description:

KeyConnect Faceplates 12-Port, w/ ID Windows, Double Gang, Flush

### Usage (Overall)

|                               |                                                                                                                                                               |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Suitable Applications:</b> | - Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, fiber and coax                              |
| <b>Related Parts:</b>         | - Compatible with REVConnect Jacks (UTP & STP), KeyConnect Jacks (UTP) and Keyconnect Multimedia Modules. See notes if using KeyConnect Shielded (STP) Jacks. |

### Physical Characteristics (Connectivity)

#### Capacity

|                       |         |
|-----------------------|---------|
| <b>Max. Capacity:</b> | 12-port |
|-----------------------|---------|

#### Access

|                          |       |
|--------------------------|-------|
| <b>Front Connection:</b> | Flush |
|--------------------------|-------|

#### Dimensions

##### Dimensions:

| Height (mm) | Width (mm) | Depth (mm) |
|-------------|------------|------------|
| 114.300     | 116.586    | 6.604      |

#### Materials

##### Materials:

| Description | Material          |
|-------------|-------------------|
| Plate       | Plastic - UL94V-0 |

#### Color

|               |             |
|---------------|-------------|
| <b>Color:</b> | Elec. White |
|---------------|-------------|

#### Weight

|                |          |
|----------------|----------|
| <b>Weight:</b> | 0.050 kg |
|----------------|----------|

#### Included Parts

|                        |                                                                      |
|------------------------|----------------------------------------------------------------------|
| <b>Included Parts:</b> | 6-32 screws, carton labels, clear windows, KeyConnect blank inserts. |
|------------------------|----------------------------------------------------------------------|

#### Packaging

|                   |                                         |
|-------------------|-----------------------------------------|
| <b>Packaging:</b> | Individually packaged in a plastic bag. |
|-------------------|-----------------------------------------|

### Mechanical Characteristics (Connectivity)

|                                        |                |
|----------------------------------------|----------------|
| <b>Connector/Hardware Retention:</b>   | 88.964 N       |
| <b>Storage Temperature Range:</b>      | -40°C To +70°C |
| <b>Installation Temperature Range:</b> | -10°C To +60°C |
| <b>Operating Temperature Range:</b>    | -10°C To +60°C |

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

|                                              |                |
|----------------------------------------------|----------------|
| <b>EU Directive 2002/95/EC (RoHS):</b>       | Yes            |
| <b>EU RoHS Compliance Date (mm/dd/yyyy):</b> | 07/01/2006     |
| <b>MII Order #39 (China RoHS):</b>           | Yes            |
| <b>Safety Listing:</b>                       | c(UL)us Listed |

#### Suitability

|                              |     |
|------------------------------|-----|
| <b>Suitability - Indoor:</b> | Yes |
|------------------------------|-----|

### Transmission Characteristics (Connectivity)

### Notes (Overall)

**Notes:** Please contact Tech Support if using Shielded KeyConnect jacks (AX104562, AX104595, AX104596) for compatibility verification.

## METRIC MEASUREMENT VERSION

## AX102257 Faceplates and Panels - KeyConnect Faceplates 12-Port w/ID Windows Double-Gang

## Product Family

## Part Numbers:

| Item Number                       | Stainless Steel | Dark Gray | Almond   | Black    | Ivory    | Elec. White | Gray     |
|-----------------------------------|-----------------|-----------|----------|----------|----------|-------------|----------|
| 1-Port w/ ID Windows Single-gang  | AX104230        | -         | AX103922 | AX104160 | AX104565 | AX102660    | AX107021 |
| 2-Port w/ ID Windows Single-gang  | AX104231        | AX104455  | AX103923 | AX104161 | AX104197 | AX102655    | AX107022 |
| 3-Port w/ ID Windows Single-gang  | -               | -         | AX103924 | AX104162 | -        | AX102661    | -        |
| 4-Port w/ ID Windows Single-gang  | AX104232        | AX104464  | AX102248 | AX104163 | AX104198 | AX102249    | AX107023 |
| 6-Port w/ ID Windows Single-gang  | AX104233        | -         | AX102250 | AX104164 | AX104199 | AX102251    | AX107024 |
| 4-Port w/ ID Windows Double-gang  | AX104479        | -         | -        | -        | -        | -           | -        |
| 6-Port w/ ID Windows Double-gang  | AX104480        | AX106594  | AX102670 | AX104165 | AX104566 | AX102671    | AX107025 |
| 12-Port w/ ID Windows Double-gang | AX104234        | -         | AX102256 | AX104166 | AX104200 | AX102257    | -        |
| 1-Port Single-gang                | AX102006        | -         | -        | -        | -        | -           | -        |
| 2-Port Single-gang                | AX102007        | -         | -        | -        | -        | -           | -        |
| 4-Port Single-gang                | AX102009        | -         | -        | -        | -        | -           | -        |
| 6-Port Single-gang                | AX102010        | -         | -        | -        | -        | -           | -        |
| 6-Port Double-gang                | AX102012        | -         | -        | -        | -        | -           | -        |
| 12-Port Double-gang               | AX102013        | -         | -        | -        | -        | -           | -        |
| Wall Mount Phone Plate            | AX104126        | -         | -        | -        | -        | AX102902    | -        |
| Single-gang Back Box 1.89 in.     | -               | -         | AX104127 | -        | -        | AX102657    | -        |
| Double-gang Back Box 1.89 in.     | -               | -         | AX104130 | AX106684 | -        | AX104131    | AX106685 |

## Put Ups and Colors:

| Item #   | Putup | Ship Weight | Color | Notes | Item Desc                   |
|----------|-------|-------------|-------|-------|-----------------------------|
| AX102257 | 1 EA  | 0.051 KG    |       |       | KCONN FACEPLATE 12-P DG WHI |

Revision Number: 1 Revision Date: 08-16-2017

© 2017 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.