

AX103912 Faceplates and Panels - FiberExpress Ultra Splice Tray 8 inches



For more Information
please call

1-800-Belden1

**General Description:**

FiberExpress Ultra 8 inches Splice Tray

Usage (Overall)

Suitable Applications:	FiberExpress Ultra Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
Related Parts:	FiberExpress Ultra 4U Rack Mount And Wall Mount Patch Panels

Physical Characteristics (Connectivity)**Capacity**

Max. Capacity:	Optimal 24 Splices
----------------	--------------------

Dimensions

Dimensions:

Height (mm)	Width (mm)	Length (mm)
13.970	114.300	203.200

Materials

Materials:

Description	Material	Color
Splice Tray	Metal	Black

Weight

Weight:	0.318 kg
---------	----------

Packaging

Packaging:	Individually packaged in a plastic bag, Shipped in cardboard box (25/box)
------------	---

Mechanical Characteristics (Connectivity)

Storage Temperature Range:	-40°C To +80°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)**Notes (Overall)**

Notes: For additional information about this product refer to product bulletin NP286, or visit our web site at <http://www.belden.com>.

Product Family

Part Numbers:

Description	Item Number
FiberExpress Ultra Splice Tray 8 inches	AX103912
FiberExpress Ultra Splice Tray 10 inches	AX103913
FiberExpress Ultra Splice Tray 12 inches	AX103914

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

METRIC MEASUREMENT VERSION

AX103912 Faceplates and Panels - FiberExpress Ultra Splice Tray 8 inches

Revision Number: 0 Revision Date: 09-11-2009

© 2018 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.