

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	15[mm]
Max. Air Flow:	7.4[CFM]
Max. Air Flow:	0.21[m3 per min]
Max. Static Pressure:	0.27[In H2O]
Max. Static Pressure:	68[Pa]
Fan Speed:	8300[RPM]
Noise:	32[dB]
Life Expectancy:	40 degree C 40,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.06[A]
Input Power:	0.7[W]
Mass:	23[g]
Tach / Locked Rotor Output:	No
Status:	Active