

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	15[mm]
Max. Air Flow:	22.2[CFM]
Max. Air Flow:	0.63[m3 per min]
Max. Static Pressure:	0.1[In H2O]
Max. Static Pressure:	25[Pa]
Fan Speed:	2800[RPM]
Noise:	32[dB]
Life Expectancy:	20 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.2[V]
Current:	0.1[A]
Input Power:	1.2[W]
Mass:	55[g]
Tach / Locked Rotor Output:	No
Status:	Active