

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	38[mm]
Nominal Voltage:	100[V]
Frequency:	50[Hz]
Max. Air Flow:	89.3[CFM]
Max. Air Flow:	2.5[m3 per min]
Max. Static Pressure:	0.26[In H2O]
Max. Static Pressure:	64.7[Pa]
Fan Speed:	2600[RPM]
Noise:	37[dB]
Life Expectancy:	25deg.C 100,000 hours[L10]
Bearing Type:	Ball Bearing
Ingress Protection:	none
Starting Voltage:	65[V]
Input Power (+10% - 20%):	15[V]
Current:	0.27[A]
Mass:	550[g]