

Detailed Specifications

Frame Width:	120[mm]
Frame Height:	120[mm]
Frame Depth:	38[mm]
Max. Air Flow:	45.2[CFM]
Max. Air Flow:	1.28[m3 per min]
Max. Static Pressure:	0.31[In H2O]
Max. Static Pressure:	76[Pa]
Fan Speed:	1950[RPM]
Noise:	38[dB]
Life Expectancy:	-20 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.2[V]
Current:	0.24[A]
Input Power:	2.9[W]
Mass:	175[g]
Tach / Locked Rotor Output:	No
Status:	Active