

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	20[mm]
Max. Air Flow:	34.6[CFM]
Max. Air Flow:	0.98[m3 per min]
Max. Static Pressure:	0.13[In H2O]
Max. Static Pressure:	33.5[Pa]
Fan Speed:	2950[RPM]
Noise:	32.5[dB]
Life Expectancy:	60 degree C 40,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	15[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.07[A]
Input Power:	1.7[W]
Mass:	85[g]
Tach / Locked Rotor Output:	Tach Output
Status:	EOL

DC Axial Fans