

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	38.4[mm]
Max. Air Flow:	123[CFM]
Max. Air Flow:	3.44[m ³ per min]
Max. Static Pressure:	0.409[In H ₂ O]
Max. Static Pressure:	102[Pa]
Fan Speed:	3200[RPM]
Noise:	49.5[dB]
Life Expectancy:	25 degree C 100,000 Hours (D00)[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	8[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.66[A]
Input Power:	7[W]
Mass:	400.07[g]
Tach / Locked Rotor Output:	Tach Output
Status:	PCN

DC Axial Fans