

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	38.4[mm]
Max. Air Flow:	102[CFM]
Max. Air Flow:	2.86[m3 per min]
Fan Speed:	2700[RPM]
Life Expectancy:	25 degree C 100,000 Hours (D00)[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	48[V]
Operating Voltage - Lower:	30[V]
Operating Voltage - Upper:	55.2[V]
Current:	0.16[A]
Input Power:	2[W]
Mass:	400[g]
Tach / Locked Rotor Output:	No
Status:	PCN