

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	38.4[mm]
Max. Air Flow:	201[CFM]
Max. Air Flow:	5.69[m3 per min]
Max. Static Pressure:	1.04[In H2O]
Max. Static Pressure:	260.5[Pa]
Fan Speed:	5100[RPM]
Noise:	62.3[dB]
Life Expectancy:	25 degree C 50,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	48[V]
Operating Voltage - Lower:	30[V]
Operating Voltage - Upper:	50.4[V]
Current:	0.83[A]
Input Power:	39.8[W]
Mass:	400[g]
Tach / Locked Rotor Output:	No
Status:	PCN