

Detailed Specifications

Frame Width:	172[mm]
Frame Height:	172[mm]
Frame Depth:	51[mm]
Max. Air Flow:	364[CFM]
Max. Air Flow:	10.31[m3 per min]
Max. Static Pressure:	2.236[In H2O]
Max. Static Pressure:	557[Pa]
Fan Speed:	5000[RPM]
Noise:	66[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Speed Control:	PWM
Nominal Voltage:	24[V]
Operating Voltage - Lower:	18[V]
Operating Voltage - Upper:	28[V]
Current:	2[A]
Input Power:	48[W]
Mass:	850[g]
IP Rating:	Non IP model
Tach / Locked Rotor Output:	Tach Output
Status:	Active

PWM Speed Control Fans