

Detailed Specifications

Frame Width:	24[mm]
Frame Height:	24[mm]
Frame Depth:	40[mm]
Operating Voltage - Lower:	20[V]
Operating Voltage - Upper:	26[V]
Rated Voltage:	24[V]
Rated Load:	20[mN per m]
Rated Speed:	6843[rpm]
Rated Current:	850[mA]
No Load Speed:	7772[rpm]
No Load Current:	145[mA]
Starting Torque:	167.4[mN per m]
Starting Current:	6047[mA]
Brush Material:	Carbon
Shaft Diameter:	2.5[mm]
Shaft Length:	25[mm]
Mass:	84[g]