





APPROVED: _____
 DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	11/25/15	
A		UPDATE SPEC.	3/7/19	AY/TW



2 Pin



3 Pin



Positions: 2 thru 15

A = .049 [1.25] X No. of Spaces

B = .049 [1.25] X No. of Spaces + .067 [1.70]

C = .049 [1.25] X No. of Spaces + .118 [3.00]

SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: White

Electrical:

Voltage rating: 125V AC/DC

Current rating: 1A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 100Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS DRAWN HR 11/25/15 CHECKED RT 11/25/15 APPROVED			DATE DATE DATE			TITLE 1.25mm CRIMP HOUSING SINGLE ROW 2 THRU 15 POSITIONS, COLOR: WHITE
SIZE X			PART NO. 125CH-B1-XX-HF			REV. A
REF: S00015T			SCALE: NTS			SHEET 1 OF 1